


APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/26/08	
A		UPDATE SPEC.	2/15/16	AY/MY



Wire Size AWG	Positions			
	2	4, 6	8, 10	12~24
#18	9A	8A	7A	6A
#20	7A	6A	5A	5A
#22	5A	4A	4A	4A
#24	4A	3A	3A	3A

#### SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: Natural

Electrical:

Operating voltage: 600 VAC max

Current rating: See chart

Insulation resistance: 1000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1500 VAC for 1 minute

Mechanical:

Wire size: 18 Awg thru 24 Awg

Temperature Rating:

Operating temperature: -40°C to 105°C

Environmental:

Lead free, RoHS compliant.



2 POSITION




8 POSITION



4 POSITION




10 POSITION




6 POSITION




12 POSITION




14 POSITION




20 POSITION




16 POSITION




22 POSITION



18 POSITION



24 POSITION



Positions: 2 thru 24

A = .165 [4.20] X No. of Spaces per row

B = .165 [4.20] X No. of Positions per row + .047 [1.20]

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE MM [INCHES]  
 TOLERANCES: EXCEPT AS NOTED  
 INCHES HOLES  
 .X ± .10 Ø.X ± .10  
 .XX ± .020 Ø.XX ± .015  
 .XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	DY	9/26/08
CHECKED		
APPROVED		

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE  
 PLUG HOUSING, DUAL ROW, .165 [4.20] PITCH  
 WITHOUT MOUNTING EARS

SIZE X	PART NO. DMF-XX-W-NE	REV. A
REF: S00123T	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DMF-06-W-NE](#) [DMF-18-W-NE](#) [DMF-12-W-NE](#) [DMF-04-W-NE](#) [DMF-16-W-NE](#) [DMF-08-W-NE](#) [DMF-10-W-NE](#)  
[DMF-24-W-NE](#) [DMF-14-W-NE](#)