





APPROVED: _____
DATE: _____ TITLE: _____



Rev	AWO #	Description	Date	Appr
-	11140	RELEASED	3/08/11	
A		UPDATE DIM. & SPEC.	6/3/17	AY/MY



4~12P
 $C = .118 [3.00] \times (N - 3) + .067 [1.70]$



RECOMMENDED PCB LAYOUT



POSITIONS	Dimension	
	A	B
2	.118 [3.00]	.380 [9.65]
3	.236 [6.00]	.498 [12.65]
4	.354 [9.00]	.616 [15.65]
5	.472 [12.00]	.734 [18.65]
6	.591 [15.00]	.852 [21.65]
7	.709 [18.00]	.970 [24.65]
8	.827 [21.00]	1.089 [27.65]
9	.945 [24.00]	1.207 [30.65]
10	1.063 [27.00]	1.325 [33.65]
11	1.181 [30.00]	1.443 [36.65]
12	1.299 [33.00]	1.561 [39.65]

SPECIFICATIONS:

Material:

Insulator: LCP, rated UL 94V-0

Insulator color: Black

Contact: Brass, Tin plated

Electrical:

Voltage rating: 250 VAC

Current rating: 5 A

Contact resistance: 10 mohms max.

Withstanding voltage: 1500 VAC for 1 minute

Temperature rise: 30°C max.

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS DATE

DRAWN DY 3/08/11

CHECKED

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.118 [3.00] SINGLE ROW HEADER
HORIZONTAL, PCB TYPE

SIZE X PART NO. DML-1-XX-A-H-T-A REV. A

REF: S00015T SCALE: NTS SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DML-1-02-A-H-T-A](#) [DML-1-06-A-H-T-A](#) [DML-1-05-A-H-T-A](#) [DML-1-04-A-H-T-A](#) [DML-1-03-A-H-T-A](#)