





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/14/15	



RECOMMENDED PCB LAYOUT



POSITIONS	Dimension	
	A	B
2	.118 [3.00]	.380 [9.65]
3	.236 [6.00]	.498 [12.65]
4	.354 [9.00]	.616 [15.65]
5	.472 [12.00]	.734 [18.65]
6	.591 [15.00]	.852 [21.65]
7	.709 [18.00]	.970 [24.65]
8	.827 [21.00]	1.089 [27.65]
9	.945 [24.00]	1.207 [30.65]
10	1.063 [27.00]	1.325 [33.65]
11	1.181 [30.00]	1.443 [36.65]
12	1.299 [33.00]	1.561 [39.65]

SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Contact: Brass, Tin plated

Electrical:

Operating voltage: 250 VAC

Current rating: 5 Amps

Contact resistance: 10 mohms max.

Withstanding voltage: 1500 VAC for 1 minute

Temperature Rating:

Ambient temperature range: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			DATE		
DRAWN	AY		10/14/15	TITLE .118 [3.00] SINGLE ROW HEADER HORIZONTAL, TIN PLATED, SMT	
CHECKED	LW		10/14/15		
APPROVED				SIZE X	PART NO. DML-1-XX-A-H-T-A-TSMT-T/R
			REF: S00123T	SCALE: NTS	REV. -
			SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DML-1-03-A-H-T-A-TSMT-T/R](#) [DML-1-02-A-H-T-A-TSMT-T/R](#) [DML-1-04-A-H-T-A-TSMT-T/R](#) [DML-1-05-A-H-T-A-TSMT-T/R](#)