




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/15/12	



PCB Layout: Component side



Dimensional Information

Unit: mm

CIRCUITS	DIM. E	DIM. F	CIRCUITS	DIM. E	DIM. F
2		6.65	14	18.0	24.65
4	3.0	9.65	16	21.0	27.65
6	6.0	12.65	18	24.0	30.65
8	9.0	15.65	20	27.0	33.65
10	12.0	18.65	22	30.0	36.65
12	15.0	21.65	24	33.0	39.65

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250V AC, DC

Current rating: 5A AC, DC

Contact resistance: 10 mohms max.



Dielectric withstanding voltage: 1500 VAC for 1 minute

Temperature Rating:

Ambient temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ±.10 Ø.X ±.10 .XX ±.020 Ø.XX ±.015 .XXX ±.015 Ø.XXX ±.010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE		
DATE		DUAL ROW, .118"(3.0MM) PITCH, SMT HOUSING & TERMINAL, W/ FITTING NAIL			
DRAWN	AY	6/15/12		SIZE	PART NO.
CHECKED	AH	6/15/12		X	DML-XX-A-H-T-A-TSMT-T/R
APPROVED				REF:	S00123T
				SCALE:	NTS
				SHEET	1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DML-06-A-H-T-A-TSMT-T/R](#) [DML-16-A-H-T-A-TSMT-T/R](#) [DML-12-A-H-T-A-TSMT-T/R](#) [DML-10-A-H-T-A-TSMT-T/R](#)
[DML-24-A-H-T-A-TSMT-T/R](#) [DML-14-A-H-T-A-TSMT-T/R](#) [DML-04-A-H-T-A-TSMT-T/R](#) [DML-08-A-H-T-A-TSMT-T/R](#)