




APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



Rev	AWO #	Description	Date	Appr
-		RELEASED	10/04/11	
A		UPDATED BOARDLOCK DIM.	2/10/17	HR/CT



SHOWN WITH CAP



RECOMMENDED PCB LAYOUT



POSITIONS	Dimension	
	A	B
2	N/A	.262 [6.65]
4	.118 [3.00]	.380 [9.65]
6	.236 [6.00]	.498 [12.65]
8	.354 [9.00]	.616 [15.65]
10	.472 [12.00]	.734 [18.65]
12	.591 [15.00]	.852 [21.65]
14	.709 [18.00]	.970 [24.65]
16	.827 [21.00]	1.088 [27.65]
18	.945 [24.00]	1.206 [30.65]
20	1.063 [27.00]	1.325 [33.65]
22	1.181 [30.00]	1.443 [36.65]
24	1.299 [33.00]	1.561 [39.65]


#### SPECIFICATIONS:

Material:  
 Insulator: Hi-temp thermoplastic, rated UL 94V-0  
 Insulator color: Black  
 Contacts: Brass  
 Plating:  
 Tin over Copper underplate on tails.

Electrical:  
 Voltage rating: 250V AC, DC  
 Current rating: 5A AC, DC  
 Contact resistance: 10 mohms max  
 Dielectric withstanding voltage: 1500 VAC for 1 minute  
 Temperature range:  
 -25°C to +85°C  
 Environmental:  
 Lead free, RoHS compliant.



#### PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES                      HOLES .X           ± .10           Ø.X           ±.10 .XX        ± .020        Ø.XX       ± .015 .XXX      ± .015       Ø.XXX      ±.010			<div>ADAM TECH</div> <div>INTERCONNECTS</div>		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			DATE		TITLE  .118 [3.00] DUAL ROW HEADER, VERTICAL SMT TYPE, WITH CAP	
DRAWN	TW	10/04/11				
CHECKED	AY	10/04/11				
APPROVED						
SIZE X		PART NO. DML-XX-A-V-T-SMT-BL-PP-T/R			REV A	
REF: S00123T			SCALE: NTS		SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DML-12-A-V-T-SMT-BL-PP-T/R](#) [DML-04-A-V-T-SMT-BL-PP-T/R](#) [DML-14-A-V-T-SMT-BL-PP-T/R](#) [DML-08-A-V-T-SMT-BL-PP-T/R](#)  
[DML-06-A-V-T-SMT-BL-PP-T/R](#) [DML-10-A-V-T-SMT-BL-PP-T/R](#) [DML-16-A-V-T-SMT-BL-PP-T/R](#)  
[DML-24-A-V-T-SMT-BL-PP-T/R](#)