





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/14/18	



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: SPCC, Nickel plated

Boardlock: Copper Alloy, Tin plated

Bracket: Zinc Alloy, Nickel plated

Plating:

Gold flash over Nickel underplate in contact area,

Tin over Nickel underplate on solder tails.

Electrical:

Operation Voltage: 250 VAC (RMS) max

Current rating: 3 Ampere per Contact

Contact resistance: 25 mohms max

Insulation resistance: 5,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC (RMS)

Temperature Rating:

Operating temperature: -55°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DRAWN	AY	DATE
CHECKED	KC	6/14/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
DUAL PORT D-SUB, 25P FEMALE OVER
25P FEMALE, FORKED BOARDLOCKS

SIZE	PART NO.	REV.
X	DPD-25-00-A3	-
REF:	S00027T	SCALE: NTS
SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DPD-25-00-A3](#)