



APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/28/05	
A		UPDATED DRAWING	4/21/15	HR/LL



DXXX	NO. OF CONTACTS	DIMENSIONS				
		A	B	C	D	E
DE09	9	.666 [16.92]	.984 [24.99]	1.213 [30.81]	.756 [19.20]	.436 [11.08]
DA15	15	.994 [25.25]	1.311 [33.30]	1.543 [39.20]	1.091 [27.70]	.763 [19.39]
DB25	25	1.534 [38.96]	1.852 [47.04]	2.088 [53.04]	1.618 [41.10]	1.309 [33.24]
DC37	37	2.182 [55.42]	2.500 [63.50]	2.732 [69.40]	2.256 [57.30]	1.963 [49.86]

SPECIFICATIONS:  
Material: Insulator: PBT, glass reinforced, rated UL 94V-0  
Insulator color: Black  
Contacts: Brass  
Front Shell: Steel, Nickel plated  
Back Shell: Steel, Tin plated  
Plating: Gold flash over Nickel underplate overall  
Electrical: Operating voltage: 250 VAC max  
Current rating: 3 Amps max  
Contact resistance: 20 mohms max  
Insulation resistance: 1,000 Mohms min @ 500 VDC  
Dielectric withstanding voltage: 1,000 VAC for 1 minute  
Environmental: Lead free, RoHS compliant



**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: D-SUB PLUG, SOLDER CUP  
MOUNTING HOLES

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		INCHES		Holes	
.X	± .10	ØX	± .10	ØXX	± .015
.XX	± .020	ØXX	± .015	ØXXX	± .010
.XXX	± .015	ØXXX	± .010		
APPROVALS		DATE			
DRAWN	SS	4/28/05			
CHECKED					
APPROVED					

SIZE	PART NO.	DXXX-PD	REV.
X			A
REF:	S00087T	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DA15-PD](#) [DE09-PD](#) [DC37-PD](#) [DB25-PD](#)