



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/25/05	
A		REVISED SPEC.	03/04/13	



Positions	DIMENSIONS			
	A	B	C	D
9	.666 [16.92]	.984 [24.99]	1.213 [30.81]	.883 [22.44]
15	.994 [25.25]	1.312 [33.32]	1.541 [39.14]	1.213 [30.81]
25	1.534 [38.96]	1.852 [47.04]	2.088 [53.04]	1.755 [44.57]
37	2.182 [55.43]	2.500 [63.50]	2.729 [69.32]	2.414 [61.32]

Unit: Inch / mm

SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Steel, Tin plated

Plating:

Gold Flash over Nickel underplate on mating area,

Tin over Copper underplate on IDC area

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 15 mohms max

Insulation resistance: 3,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Mechanical:

Recommended cable size: 28-30 AWG

Temperature Rating:

Operating temperature: -55°C to +125°C

Environmental:

Lead free, RoHS compliant

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

IDC FLAT CABLE D-SUB PLUG

METAL SHELL, .130 [3.30] MOUNTING HOLES

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				HOLE SIZES							
.X	± .10	Ø.X	± .10	.XX	± .020	Ø.XX	± .015	.XXX	± .015	Ø.XXX	± .010
APPROVALS				DATE							
DRAWN	SS	4/25/05									
CHECKED											
APPROVED											
SIZE				PART NO.				REV.			
X				DXXX-PF-M1				A			
REF: S00013T				SCALE: NTS				SHEET 1 OF 1			

ADAM TECH	
909 Rahway Avenue, Union, NJ 07083	
Phone: 908-687-5000 Fax: 908-687-5710	
IDC FLAT CABLE D-SUB PLUG	
METAL SHELL, .130 [3.30] MOUNTING HOLES	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DE09-PF-M1](#) [DC37-PF-M1](#) [DA15-PF-M1](#) [DB25-PF-M1](#)