




Rev	AWO #	Description	Date	Appr
-		RELEASED	4/25/05	
A		REDRAWN	4/03/09	
B		REDRAWN	8/2/11	

APPROVED: _____
DATE: _____ TITLE: _____



Unit: Inch / mm

Positions	DIMENSIONS			
	A	B	C	D
9	.666 [16.92]	.984 [25.00]	1.213 [30.80]	.882 [22.40]
15	.994 [25.25]	1.311 [33.30]	1.543 [39.20]	1.213 [30.80]
25	1.534 [38.96]	1.854 [47.10]	2.091 [53.10]	1.752 [44.50]
37	2.182 [55.43]	2.500 [63.50]	2.732 [69.40]	2.417 [61.40]

SPECIFICATIONS:

Material:

Insulator: Thermal Plastic, rated UL 94V-0

Contacts: Copper Alloy

Shell: Steel, Tin plated

Rivet Boardlock: Copper Alloy

Plating:

Gold over Nickel underplate on mating area,
Tin over Copper underplate on IDC area

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 15 mohms max

Insulation resistance: 3,000 Mohms min @500 VDC

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

IDC FLAT CABLE D-SUB PLUG
METAL SHELL, #4-40 THD MOUNTING HOLES

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		INCHES		Holes	
.X	± .10	ØXX	± .10		
.XX	± .020	ØXXX	± .015		
.XXX	± .015	ØXXX	± .010		
APPROVALS		DATE		TITLE	
DRAWN	SS	4/25/05		SIZE	
CHECKED				PART NO.	
APPROVED				DXXX-PF-M2	
REF: S00013T		SCALE: NTS		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DC37-PF-M2](#) [DE09-PF-M2](#) [DA15-PF-M2](#) [DB25-PF-M2](#)