




APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/29/05	
A		REDRAWN	04/16/12	



DXXX	NO. OF CONTACTS	DIMENSIONS			
		A	B	C	D
DE09	9	.666 [16.92]	.984 [24.99]	1.213 [30.81]	.436 [11.08]
DA15	15	1.004 [25.50]	1.312 [33.32]	1.541 [39.14]	.763 [19.39]
DB25	25	1.534 [38.96]	1.852 [47.04]	2.088 [53.04]	1.309 [33.24]
DC37	37	2.182 [55.42]	2.500 [63.50]	2.729 [69.32]	1.963 [49.86]

SPECIFICATIONS:  
Material: Insulator: PBT, glass reinforced, rated UL 94V-0  
Insulator color: Black  
Contacts: Copper Alloy  
Shell: Steel, Tin plated  
Plating:  
Gold flash over Nickel underplate overall.  
Electrical:  
Insulation resistance: 1,000 Mohms min  
Dielectric withstanding voltage: 1,000 VAC for 1 minute  
Operating temperature: -55°C to +105°C  
Environmental:  
Lead free, RoHS compliant



**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

D-SUB PLUG, CRIMP AND POKE  
.120 [3.05] MOUNTING HOLES

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		TITLE	
.X INCHES ± .10 .XX ± .020 .XXX ± .015	ØX HOLE5 ± .10 ØXXX ± .015 ØXXX ± .010	DATE	REV.
DRAWN	SS	4/29/05	
CHECKED			
APPROVED			
SIZE	PART NO.	DXXX-PR	A
REF:	S00087T	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DA15-PR](#) [DB25-PR](#) [DC37-PR](#) [DE09-PR](#)