





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/13/05	
A		REDRAWN	07/17/13	
B		UPDATED DRAWING	7/25/18	HR/MY



SPECIFICATIONS:

Material:

Insulator: PBT, Thermoplastic, glass filled, rated UL 94V-0

Insulator color: Black

Contacts: Copper alloy

Shell: Steel, Tin plated

Boardlock: Brass, Tin plated

Plating:

Gold flash over Nickel underplate on contact area.

Electrical:

Voltage rating: 250 VAC/rms

Current rating: 3 Amp

Contact resistance: 20 mohms

Insulation resistance: 1,000 Mohms @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



DXXX	NO. OF CONTACTS	DIMENSIONS				
		A	B	C	D	E
DE09	9	1.213 [30.81]	.984 [24.99]	.666 [16.92]	.436 [11.08]	.756 [19.20]
DA15	15	1.543 [39.20]	1.311 [33.30]	.994 [25.25]	.763 [19.39]	1.091 [27.70]
DB25	25	2.088 [53.04]	1.852 [47.04]	1.534 [38.96]	1.309 [33.24]	1.618 [41.10]
DC37	37	2.732 [69.40]	2.500 [63.50]	2.182 [55.42]	1.963 [49.86]	2.256 [57.30]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE	
DRAWN	SS	4/13/05	
CHECKED			
APPROVED			

TITLE		D-SUB PLUG, STANDARD PROFILE RIVETED #4-40 STANDOFFS W/BOARDLOCKS	
SIZE	PART NO.	REV.	
X	DXXX-PT-1-BL	B	
REF:	S00087T	SCALE:	NTS
SHEET 1 OF 1			

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DA15-PT-1-BL](#) [DE09-PT-1-BL](#) [DB25-PT-1-BL](#)