



Rev	AWO #	Description	Date	Appr
-		RELEASED	4/18/05	
A		UPDATED	4/19/11	
B		REVISED DIM.	10/12/11	

APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



Dimensions

Positions	A	B	C
09	.643 [16.33]	.984 [24.99]	1.213 [30.81]
15	.971 [24.66]	1.312 [33.32]	1.541 [39.14]
25	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]
37	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]

SPECIFICATIONS:

Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy
Shell: SPC
Hardware: Brass, Nickel plated
Plating:
Gold flash over Nickel underplate overall.
Electrical:
Operating voltage: 250 VAC
Current rating: 1 Amp
Contact resistance: 20 mohms max
Insulation resistance: 1,000 Mohms @ 500VAC
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -65°C to +125°C
Environmental:
Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
D-SUB, SOCKET, FLUSH MOUNT
#4-40 THREADED FLUSH INSERTS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
INCHES			
.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010
APPROVALS		DATE	
DRAWN	SS	4/18/05	
CHECKED			
APPROVED			
SIZE		PART NO.	REV.
X		DXXX-SA-M2	B
REF:		SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DA15-SA-M2](#) [DE09-SA-M2](#) [DB25-SA-M2](#)