





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/19/04	
A		REDRAWN	7/20/10	
B		REVISED DIM.	07/05/12	
C		REVISED SPEC.	3/22/13	



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy
Shell: Steel, Tin plated
Cinch Nut: Copper Alloy, Nickel plated
Boardlock: Brass, Tin plated
Plating:

Gold over Nickel underplate on contact area
Electrical:

Operating voltage: 250 VAC max
Current rating: 3 Amps max
Contact resistance: 20 mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -20°C to +85°C
Environmental:
Lead free, RoHS compliant

DXXX	NO. OF CONTACTS	DIMENSIONS		
		A	B	C
DE09	9	.643 [16.33]	.984 [24.99]	1.213 [30.81]
DA15	15	.972 [24.70]	1.311 [33.30]	1.543 [39.20]
DB25	25	1.512 [38.40]	1.852 [47.04]	2.089 [53.05]
DC37	37	2.157 [54.80]	2.500 [63.50]	2.732 [69.40]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		TITLE D-SUB SOCKET, .318" FOOTPRINT, FORKED BOARD LOCKS, #4-40 FLUSH THREADED INSERTS	
INCHES	HOLES	SIZE	PART NO.
.X ± .10	ϕ X ± .10	X	DXXX-SL-24
.XX ± .020	ϕ XX ± .015		
.XXX ± .015	ϕ XXX ± .010		
APPROVALS	DATE	REV.	C
DRAWN	SS	10/19/04	
CHECKED			
APPROVED			
REF: S00087T	SCALE: NTS	SHEET 1 OF 1	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DB25-SL-24](#) [DE09-SL-24](#) [DA15-SL-24](#) [DC37-SL-24](#)