




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/19/05	
A		CHART REVISION	7/29/13	



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: Steel, Tin plated

Clinch Nut: Brass, Nickel plated

Boardlock: Brass, Tin plated

Screwlock: Brass, Nickel plated

Plating:

Gold over Nickel underplate on contact area

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Environmental:

Lead free, RoHS compliant



DXXX	NO. OF CONTACTS	DIMENSIONS		
		A	B	C
DE09	9	.643 [16.33]	.984 [24.99]	1.213 [30.81]
DA15	15	.971 [24.66]	1.312 [33.32]	1.541 [39.14]
DB25	25	1.493 [38.38]	1.852 [47.04]	2.088 [53.04]
DC37	37	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

Phone: 908-687-5000 Fax: 908-687-5710

318 [8.06] FOOTPRINT D-SUB SOCKET
FORKED BOARDLOCKS, #4-40 INSERTS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES		TITLE	
.X ± .10 ØXX ± .10	HOLE	.318 [8.06] FOOTPRINT D-SUB SOCKET	
.XX ± .020 ØXXX ± .015	HOLE	FORKED BOARDLOCKS, #4-40 INSERTS	
.XXX ± .015 ØXXXX ± .010	HOLE		
APPROVALS	DATE		
DRAWN	SS	4/19/05	
CHECKED			
APPROVED			
SIZE	PART NO.	DXXX-SL-25	
REF: S00087T	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DE09-SL-25](#) [DA15-SL-25](#) [DB25-SL-25](#) [DC37-SL-25](#)