





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	04/27/06	
A		REDRAWN	03/28/13	



SPECIFICATIONS:

Material: Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Shell: Steel, Tin plated
Cinch Nut: Brass, Nickel plated
Screwlock: Brass, Nickel plated
Plating: Gold flash over Nickel underplate overall
Electrical: Operating voltage: 250 VAC max
Current rating: 3 Amps max
Contact resistance: 20 mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating: Operating temperature: -55°C to +85°C
Environmental: Lead free, RoHS compliant

Positions	DIMENSIONS				
	A	B	C	D	E
9	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.756 [19.20]	.436 [11.08]
15	.972 [24.70]	1.311 [33.30]	1.543 [39.20]	1.091 [27.70]	.763 [19.39]
25	1.512 [38.40]	1.852 [47.04]	2.089 [53.05]	1.618 [41.10]	1.309 [33.24]
37	2.157 [54.80]	2.500 [63.50]	2.732 [69.40]	2.256 [57.30]	1.963 [49.86]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 ØX ± .10 .XX ± .020 ØXX ± .015 .XXX ± .015 ØXXX ± .010				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710					
APPROVALS		DATE		TITLE D-SUB SOCKET, STANDARD PROFILE RIVETED #4-40 JACKSCREWS					
DRAWN		LFI							
CHECKED									
APPROVED				SIZE		PART NO.		REV.	
				X		DXXX-ST-1-JS		A	
REF: S00087T				SCALE: NTS		SHEET 1 OF 1			



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DE09-ST-1-JS](#) [DB25-ST-1-JS](#)