



Rev	AWO #	Description	Date	Appr
-		RELEASED	10/19/04	

APPROVED: _____
DATE: _____ TITLE: _____



DXXX	NO. OF CONTACTS	DIMENSION			
		A	B	C	D
DE09	9	.642 [16.33]	.984 [25.00]	1.21 [30.81]	.76 [19.20]
DA15	15	.969 [24.66]	1.312 [33.32]	1.54 [39.20]	1.09 [27.70]
DB25	25	1.508 [38.38]	1.852 [47.04]	2.09 [53.10]	1.62 [41.10]
DC37	37	2.157 [54.84]	2.500 [63.5]	2.73 [69.40]	2.26 [57.30]

SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating:

Gold Flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 5000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC for 1 minute

Temperature Rating:

Operating temperature: -65°C to +125°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES Holes
X ± .10 ØXX ± .10
.XX ± .020 ØXX ± .015
.XXX ± .015 ØXXX ± .010

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

D-SUB, STRAIGHT, FEMALE,
STANDARD TAILS, GOLD FLASH PLATED

APPROVALS		DATE		TITLE	
DRAWN	SS	10/19/04		D-SUB, STRAIGHT, FEMALE, STANDARD TAILS, GOLD FLASH PLATED	
CHECKED				SIZE PART NO. DXXX-ST-1-SL	
APPROVED				REV. -	

REF:	SCALE: NTS	SHEET 1 OF 1
------	------------	--------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DB25-ST-1-SL](#) [DA15-ST-1-SL](#) [DE09-ST-1-SL](#) [DC37-ST-1-SL](#)