

6

5

4

3


2

1





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	



RECOMMENDED PCB LAYOUT



WITHOUT COVER

SPECIFICATIONS:**Material:**

Insulator: PA, rated UL 94V-0

Insulator color: Green

Contact: Copper Alloy, Tin plated

Electrical:

Voltage rating: 300V

Current rating: 20A

Dielectric withstanding voltage: 1,600 VAC for 1 minute

Mechanical:

Strip length: 9~10mm

Wire Range: 24~12 AWG

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 01 thru XX

A= .197 [5.00] x No. of Positions + .055 [1.40]

B= .197 [5.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS**DATE**

DRAWN	AY	11/26/18
CHECKED	AC	11/26/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

EURO BLOCK, .197 [5.00] PITCH, HORIZONTAL

SIZE
X

PART NO.

EB163A-XX-C

REV.
-

REF: S00067C

SCALE: NTS

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EB163A-03-C](#) [EB163A-05-C](#) [EB163A-02-C](#) [EB163A-04-C](#) [EB163A-06-C](#)