







APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	



SPECIFICATIONS:

Material:
 Insulator: PA, rated UL 94V-0
 Insulator color: Green
 Contact: Copper Alloy, Tin plated
 Electrical:
 Voltage rating: 600 V
 Current rating: 66 A
 Dielectric withstanding voltage: 2,200 VAC for 1 minute
 Mechanical:
 Strip length: 18~19mm
 Wire Range: 4~18 AWG
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.



Poles: 01 thru XXP
 A = .394 [10.00] X No. of Positions +.071 [1.80]
 B = .394 [10.00] X No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010		ADAM TECH INTERCONNECTS		909 Rahway Avenue,			
				Union, NJ 07083			
				Phone: 908-687-5000			
				Fax: 908-687-5710			
APPROVALS		DATE		TITLE			
DRAWN	AY	11/26/18					
CHECKED	AC	11/26/18					
APPROVED							
		SIZE		PART NO.		REV.	
		X		EB167A-XX-H		-	
		REF: S00067C		SCALE: NTS		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EB167A-06-H](#) [EB167A-04-H](#) [EB167A-02-H](#) [EB167A-05-H](#) [EB167A-03-H](#)