






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	
A		UPDATE DRAWING	5/9/19	LH/KC



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: PA, rated UL 94V-0

Insulator color: Green

Pin Header: Copper Alloy, Tin plated

Electrical:

Voltage rating: 600 V

Current rating: 51 A

Dielectric withstanding voltage: 2,200 V for 1 minute

Mechanical:

Wire range: 18~4AWG

Wire strip length: 17~18mm

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 24

A= .394 [10.00] x No. of Positions + .055 [1.40]

B= .394 [10.00] x No. of Space

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	AY	11/26/18
CHECKED	AC	11/26/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE
 .394 [10.00] PITCH SPRING CLAMP
 TERMINAL BLOCKS, RIGHT ANGLE

SIZE	PART NO.	REV.
X	EB171A-XX-H	A
REF: S00067C	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EB171A-02-H](#) [EB171A-06-H](#) [EB171A-04-H](#) [EB171A-03-H](#) [EB171A-05-H](#)