





Rev	AWO #	Description	Date	Appr
-		RELEASED	10/22/14	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Contact: Brass, Tin plated

Shrapnel: Phosphor Bronze, Nickel plated

Screw: M3 Steel, Zinc plated

Electrical:

Operational voltage: 250 VAC max

Current rating: 16 Amps

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min @ 500 VDC

Dielectric withstanding voltage: 2,000 VAC for 1 minute

Wire range: 22-14AWG, 1.5mm²

Mechanical:

Torque: 0.5Nm (4.5Lb.In)

Strip length: 4-4.5mm

Temperature Rating:

Operating temperature: -30°C to +120°C

Environmental:

Lead free, RoHS compliant.

ROHS
COMPLIANT

Positions: 02 thru 24
A = .197 [5.00] x No. of Positions
B = .197 [5.00] x No. of Spaces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE

.197" [5.00] PITCH, TERMINAL BLOCK

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØX	± .10	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN	AY		10/22/14	CHECKED	MW		10/22/14
APPROVED							
SIZE				PART NO.			
X				EBAA-XX-C			
REF: S00067C				SCALE: NTS			
				SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EBAA-02-C](#) [EBAC-03-C](#)