





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/29/14	
A		UPDATE SPEC.	8/22/17	AY/RC1
B		UPDATE DRAWING	2/13/20	AY/RT
C		UPDATE DRAWING	2/23/21	LH/EY



SECTION A-A



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Blue

Screw: M2.5, Steel, Zinc plated.

Contact: Copper Alloy, Tin plated.

Shrapnel: Stainless Steel

Electrical:

Voltage rating: 250 V

Current rating: 16 A

Withstanding voltage: 1,500 VAC for 1 minute

Mechanical:

Torque: 0.4N-m

Wire Range: 22-14AWG

Strip Length: 5-6mm

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 24

A = .197 [5.00] x No. of Positions

B = .197 [5.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	AY	9/29/14
CHECKED	GC	9/29/14
APPROVED		

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

EURO BLOCK, .197 [5.00] PITCH, SLOTTED SCREW

SIZE X	PART NO. EBBA-XX-C-SS-BU	REV. C
REF: S00067C	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EBBA-03-C-SS-BU](#) [EBBA-04-C-SS-BU](#) [EBBA-05-C-SS-BU](#) [EBBA-06-C-SS-BU](#) [EBBA-02-C-SS-BU](#)