




APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/2/13	
A		UPDATE DRAWING	7/9/18	AY/KC



SECTION A-A



SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Cage: Brass, Nickel plated

Screw: Steel, M3.0/Zinc plated

Clamp: Phosphor Bronze, Nickel plated

Electrical:

Voltage rated: 300V

Current rated: 15A

Contact resistance: 20 mΩ

Insulation resistance: 500 MΩ @ 500 VDC

Withstanding voltage: 2000V AC/1 Min

Mechanical:

Solid wire: 28-14AWG 1.5mm²

Torque (Lb-In): 0.5Nm (4.5lb-in)

Strip length: 7-8mm

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Poles: 2 thru 24

A = .197 [5.00] x No. of Poles

B = .197 [5.00] x No. of (Poles - 1)

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	AY	8/2/13
CHECKED	NP	8/2/13
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.197 [5.00] TERMINAL BLOCK, SLOTTED SCREW

SIZE X	PART NO. EBHA-XX-C	REV. A
REF: S00067C	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EBHA-05-C](#) [EBHA-03-C](#) [EBHA-06-C](#) [EBHA-07-C](#) [EBHA-04-C](#) [EBHA-02-C](#) [EBHA-10-C](#)