





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/13/14	
A		UPDATE SPEC.	8/27/15	AY
B		UPDATE DRAWING	4/11/17	AY
C		UPDATE DRAWING	12/8/20	LH/EY



SECTION A-A

SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Contact: Copper Alloy ,Nickel Plated

Screw: M2

Electrical:

Voltage rating: 300V

Current rating: 8 Amp

Dielectric withstanding voltage: 1,600 VAC for 1 minute

Mechanical:

Wire range: 16-28 AWG

Torque: 0.2Nm

Strip length: 6-7mm

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 24

A = .138 [3.50] x No. of Spaces + .169 [4.30]

B = .138 [3.50] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
					TITLE			
			APPROVALS		DATE		PLUGGABLE BLOCK, PITCH .138 [3.50]	
			DRAWN	AY	6/13/14			
CHECKED			SIZE X	PART NO. EBKA-XX-A		REV. C		
APPROVED			REF: S00067C	SCALE: NTS	SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EBKA-04-A](#) [EBKA-05-A](#) [EBKA-07-A](#) [EBKA-12-A](#) [EBKA-03-A](#) [EBKA-02-A](#) [EBKA-06-A](#)