





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/2/14	
A		REVISED DIM.	6/4/14	HR/VY
B		UPDATE SPEC.	8/27/15	AY
C		UPDATE DRAWING	4/11/17	AY
D		UPDATE SPEC.	7/28/20	AY/EY



SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Screws: M2

Contact material: Copper Alloy, Nickel plated

Electrical:

Voltage rating: 300 V

Current rating: 8 A

Dielectric withstanding voltage: 1,600 V for 1 minute

Mechanical:

Wire range: 28-16 AWG

Torque: 0.2 N.m max

Wire strip length: 6-7mm

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 24

A = .150 [3.81] x No. of Spaces + .181 [4.60]

B = .150 [3.81] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	HR	5/2/14
CHECKED	SY	5/2/14
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
PLUGGABLE BLOCK, PITCH .150 [3.81]

SIZE X	PART NO. EBKA-XX-B	REV. D
REF: S00067C	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EBKA-06-B](#) [EBKA-03-B](#) [EBKA-16-B](#) [EBKA-14-B](#) [EBKA-05-B](#) [EBKA-09-B](#) [EBKA-08-B](#) [EBKA-04-B](#) [EBKA-15-B](#)
[EBKA-02-B](#)