





APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

| Rev | AWO # | Description    | Date     | Appr  |
|-----|-------|----------------|----------|-------|
| -   |       | RELEASED       | 10/16/13 |       |
| A   |       | UPDATE DRAWING | 10/26/18 | AY/KC |
| B   |       | UPDATE SPEC.   | 9/9/20   | OW/EY |



SECTION A-A

Positions: 02 thru 24

A = .200 [5.08] x No. of Positions

B = .200 [5.08] x No. of Spaces

#### SPECIFICATIONS:

##### Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Contact: Copper Alloy, Tin plated.

##### Electrical:

Voltage rated: 300 V

Current rated: 15 A

Dielectric withstanding voltage: 1600V for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE MM [INCHES]  
TOLERANCES: EXCEPT AS NOTED

| INCHES |        | HOLES |        |
|--------|--------|-------|--------|
| .X     | ± .10  | Ø.X   | ± .10  |
| .XX    | ± .020 | Ø.XX  | ± .015 |
| .XXX   | ± .015 | Ø.XXX | ± .010 |

| APPROVALS |    | DATE     |
|-----------|----|----------|
| DRAWN     | AY | 10/16/13 |
| CHECKED   | NP | 10/16/13 |
| APPROVED  |    |          |

**ADAM**  
**TECH**  
INTERCONNECTS

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE  
TERMINAL BLOCK, SOCKETS .200 [5.08] PITCH  
VERTICAL

|              |                       |              |
|--------------|-----------------------|--------------|
| SIZE<br>X    | PART NO.<br>EBPA-XX-D | REV.<br>B    |
| REF: S00067C | SCALE: NTS            | SHEET 1 OF 1 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EBPA-03-D](#) [EBPA-04-D](#) [EBPA-02-D](#) [EBPA-05-D](#)