



Rev	AWO #	Description	Date	Appr
-		RELEASED	1/13/15	


APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED P.C.B. LAYOUT



SECTION A-A



SPECIFICATIONS:
Material:
Insulator: PA66, rated UL 94V-0
Insulator color: Green
Contact: Brass, Tin plated
Screw: Steel, M2/Zinc plated
Electrical:
Voltage rated: 300 VAC max
Current rated: 10 Amps max
Contact resistance: 20 mΩ
Insulation resistance: 500 MΩ/ 500VDC
Withstanding voltage: 2000 VAC for 1 minute
Mechanical:
Torque: 0.2Nm (1.8 lb.in)
Wire Range: 28-16Awg 1.0mm²
Strip Length: 4-5mm
Environmental:
Operating temperature: -40°C to +105°C
Lead free, RoHS compliant.



Positions: 2 thru 24
A = .150 [3.81] x No. of Positions
B = .150 [3.81] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES X ± .10 ØX ± .10 XX ± .020 ØXX ± .015 XXX ± .015 ØXXX ± .010		TITLE TERMINAL BLOCK, PCB, VERTICAL, .150 [3.81] PITCH	
APPROVALS		DATE	
DRAWN	AY	1/13/15	
CHECKED	GC	1/13/15	
APPROVED			
REF: S00067C		SCALE: NTS	SHEET 1 OF 1

ADAM TECH

909 Ridgway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EBWA-04-B](#) [EBWA-02-B](#) [EBWA-05-B](#) [EBWA-06-B](#) [EBWA-03-B](#) [EBWA-07-B](#)