


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/10	
A		REVISED DIM.	3/31/11	
B		UPDATE DRAWING	8/3/18	AY/RC1



Positions for .300 [7.62] spacing: 8, 10, 14, 16, 18, 20, 24, 28, 34, 40
 A = .100 [2.54] x No. of Spaces + .307 [7.80]
 B = .100 [2.54] x No. of Spaces

SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Voltage rating: 250 VAC/DC.

Current rating: 1A AC/DC.

Contact resistance: 20 mohms max.

Insulation resistance: 1,000 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES

.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS

DATE

DRAWN	AY	11/23/10
CHECKED	AW	11/23/10
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE
 FLAT CABLE DIP PLUG, .100 [2.54mm]
 .300 [7.62mm] ROW TO ROW

SIZE X	PART NO. FDP-3XX-T	REV. B
REF: S00040T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[FDP-308-T](#) [FDP-314-T](#) [FDP-316-T](#) [FDP-328-T](#) [FDP-324-T](#) [FDP-310-T](#) [FDP-320-T](#) [FDP-318-T](#)