







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/18/19	
A		UPDATED DRAW	3/11/19	AY/TW



Bottom Cover and Terminal

FH-A-A01
(1) (2) (3)(4)

- (1). SERIES NO.
(2). TYPE
(3). CONTACT TYPE
A=.250" [6.35mm]
(4). FUSE TYPE
01=5x20

SPECIFICATIONS:

Material:

Insulator: Thermoplastic, rated UL94V-0

Insulator color: Black (Top and Bottom)

Contact: Phosphor Bronze, Tin plated

Fuse: 5x20mm, 250V, 0.5 Amp

Temperature Rating:

Operating temperature: -20°C to +70°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ±.10 Ø.X ±.10
.XX ±.020 Ø.XX ±.015
.XXX ±.015 Ø.XXX ±.010

APPROVALS		DATE
DRAWN	AY	1/18/19
CHECKED	TW	1/18/19
APPROVED		

**ADAM
TECH**
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
FUSE HOLDER, .250" QD
5X20 FUSE, 250V 0.5 Amp

SIZE	PART NO.	REV.
X	FH-A-A01A	A
REF:	S00181C	SCALE: NTS
SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[FH-A-A01A](#)