







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/18/19	
A		UPDATED DRWN	3/11/19	AY/TW



Bottom Cover and Terminal

- FH-A-A01
 (1) (2) (3)(4)
 (1). SERIES NO.
 (2). TYPE
 (3). CONTACT TYPE
 A=.250" [6.35mm]
 (4). FUSE TYPE
 01=5x20

SPECIFICATIONS:

Material:

Insulator: Thermoplastic, rated UL94V-0

Insulator color: Black (Top and Bottom)

Contact: Phosphor Bronze, Tin plated

Fuse: 5x20mm, 250V, 6 Amp

Temperature Rating:

Operating temperature: -20°C to +70°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	Ø.X ±.10
.XX ±.020	Ø.XX ±.015
.XXX ±.015	Ø.XXX ±.010

APPROVALS		DATE
DRAWN	AY	1/18/19
CHECKED	TW	1/18/19
APPROVED		

**ADAM
 TECH**
 INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE
 FUSE HOLDER, .250" QD
 5X20 FUSE, 250V 6 Amp

SIZE	PART NO.	REV.
X	FH-A-A01C	-
REF:	S00181C	SCALE: NTS
		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[FH-A-A01C](#)