





Rev	AWO #	Description	Date	Appr
-		RELEASED	1/13/05	

APPROVED: _____

DATE: _____ TITLE: _____



SEC A-A



SEC B-B

SPECIFICATIONS:

Material:

Contact: Phosphor Bronze

Plating:

Gold flash over Nickel underplate

Electrical:

Operating voltage: 250 VAC max

Current rating: 5 Amps max

Contact resistance: 20 mohms max initial

Mechanical:

Recommended wire range: 24-26 AWG

Temperature Rating:

Operating temperature: -65°C to +125°C

Environmental:

Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

HIGH DENSITY D-SUB PLUG CONTACT

24-26 AWG

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES		TITLE	
.X ± .10	ØX ± .10	HIGH DENSITY D-SUB PLUG CONTACT	
.XX ± .020	ØXX ± .015	24-26 AWG	
.XXX ± .015	ØXXX ± .010	ADCP-01-R	
APPROVALS	DATE	REV. -	
DRAWN SS	1/13/05	PART NO.	
CHECKED		SIZE X	
APPROVED		REF: SCALE: NTS	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[HDCP-01-R](#)