





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/5/05	
A		UPDATED DRAWING	5/27/16	HR/CT



Positions	DIMENSIONS						
	A	B	C	D	E	F	G
15	.666 [16.92]	.984 [24.99]	1.213 [30.81]	.756 [19.20]	.090 [2.29]	.045 [1.145]	.277 [7.04]
26	1.004 [25.50]	1.312 [33.32]	1.541 [39.14]	1.091 [27.70]	.090 [2.29]	.045 [1.145]	.271 [6.88]
44	1.534 [38.96]	1.852 [47.04]	2.088 [53.04]	1.618 [41.10]	.090 [2.29]	.045 [1.145]	.271 [6.88]
62	2.182 [55.42]	2.500 [63.50]	2.729 [69.32]	2.256 [57.30]	.095 [2.41]	.047 [1.205]	.276 [7.00]

SPECIFICATIONS:

Material:
 Insulator: PBT, glass reinforced, rated UL 94V-0
 Insulator color: Black
 Contacts: Copper Alloy
 Shell: SPCC
 Plating:
 Gold flash over Nickel underplate on contact area
 Electrical:
 Operating voltage: 250 VAC
 Current rating: 1 Amps
 Contact resistance: 20 mohms max @ DC 100 mA
 Insulation resistance: 1,000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 500 VAC for 1 minute
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS DRAWN SS CHECKED APPROVED				TITLE HIGH DENSITY D-SUB PLUG, PCB TAILS SIZE X PART NO. HDTXX-PT REF: S00087T SCALE: NTS SHEET 1 OF 1		
DATE 5/5/05				REV. A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[HDT15-PT](#) [HDT26-PT](#) [HDT44-PT](#)