



Rev	AWO #	Description	Date	Appr
-		RELEASED	11/15/043	

65
54
43
32
21

APPROVED: _____
DATE: _____ TITLE: _____



POSITIONS	Socket Dimensions			
	A	B	C	D
15	.643 (16.33)	.984 (24.99)	1.213 (30.81)	.759 (19.28)
26	.971 (24.66)	1.312 (33.32)	1.541 (39.14)	1.083 (27.51)
44	1.511 (38.38)	1.852 (47.04)	2.008 (53.04)	1.626 (41.30)
62	2.159 (54.84)	2.500 (63.50)	2.729 (69.32)	2.272 (57.71)

Unit: Inch / mm

SPECIFICATIONS:

Material: Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Gold Flash over Nickel underplate overall
Electrical: Operating voltage: 250 VAC max
Current rating: 5 Amps max
Insulation resistance: 5000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1000 VAC for 1 minute
Temperature Rating: Operating temperature: -65°C to +125°C

A

B

C

D

A

B

C

D

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: D-SUB, HIGH DENSITY, STRAIGHT
FEMALE SOLDER CUP

DRAWN	SS	11/15/04	SIZE	PART NO.	HDTXX-SD-JS	REV.
CHECKED			X			-
APPROVED			REF:	SCALE:	NTS	SHEET 1 OF 1

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[HDT44-SD-JS](#)