


APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/11/05	
A		REDRAWN	10/8/12	



HDTXX	DIMENSIONS				
	A	B	C	D	E
15	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.756 [19.20]	.090 [2.29]
26	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	1.091 [27.70]	.090 [2.29]
44	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.618 [41.10]	.090 [2.29]
62	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	2.256 [57.30]	.095 [2.41]

SPECIFICATIONS:  
Material:  
Insulator: PBT, glass reinforced, rated UL 94V-0  
Insulator color: Black  
Contacts: Copper Alloy  
Shell: Steel, Tin plated  
Chinich Nut: Brass, Nickel plated  
Screwlock: Brass, Nickel plated  
Plating:  
Gold flash over Nickel underplate overall  
Electrical:  
Insulation resistance: 1,000 Mohms min @500 VDC  
Dielectric withstanding voltage: 1,000 VAC for 1 minute  
Environmental:  
Lead free, RoHS compliant

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

HIGH DENSITY D-SUB SOCKET  
CRIMP & POKE, .120 [3.05] MOUNTING HOLES

APPROVALS		DATE		TITLE	
DRAWN	SS	5/11/05		HIGH DENSITY D-SUB SOCKET	
CHECKED				CRIMP & POKE, .120 [3.05] MOUNTING HOLES	
APPROVED				ADAM TECH	

SPECIFICATIONS:  
Material:  
Insulator: PBT, glass reinforced, rated UL 94V-0  
Insulator color: Black  
Contacts: Copper Alloy  
Shell: Steel, Tin plated  
Chinich Nut: Brass, Nickel plated  
Screwlock: Brass, Nickel plated  
Plating:  
Gold flash over Nickel underplate overall  
Electrical:  
Insulation resistance: 1,000 Mohms min @500 VDC  
Dielectric withstanding voltage: 1,000 VAC for 1 minute  
Environmental:  
Lead free, RoHS compliant

ROHS  
COMPLIANT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[HDT15-SR](#) [HDT44-SR](#) [HDT26-SR](#)