





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/25/05	
A		REDRAWN	10/30/13	AY/NP



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Gold flash over Nickel underplate overall
Electrical: Current rating: 1 Amp max.
Contact resistance: 20 mohms max. initial
Insulation resistance: 1,000 Mohms min.
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant

Positions: 02 thru 50
A = .050 [1.27] x No. of Positions + .016 [0.40]
B = .050 [1.27] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				Holes			
.X	± .10	ØXX	± .10	.XX	± .020	ØXXX	± .015	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE							
DRAWN				SS				5/25/05			
CHECKED											
APPROVED											
TITLE				SIZE				PART NO.			
.050 [1.27] SINGLE ROW RECEPTACLE STRIP				X				HRS-1B-XX-GA			
LOW PROFILE, GOLD PLATED				REF: S00019C				SCALE: NTS			
								SHEET 1 OF 1			

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710



ROHS
COMPLIANT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[HRS-1B-12-GA](#) [HRS-1B-03-GA](#) [HRS-1B-20-GA](#) [HRS-1B-04-GA](#) [HRS-1B-18-GA](#) [HRS-1B-19-GA](#) [HRS-1B-08-GA](#)
[HRS-1B-14-GA](#) [HRS-1B-17-GA](#) [HRS-1B-07-GA](#) [HRS-1B-15-GA](#) [HRS-1B-06-GA](#) [HRS-1B-10-GA](#) [HRS-1B-21-GA](#)
[HRS-1B-16-GA](#) [HRS-1B-09-GA](#) [HRS-1B-11-GA](#) [HRS-1B-13-GA](#) [HRS-1B-05-GA](#)