

6

5

4

3




2

1


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	



RECOMMENDED PCB LAYOUT



PACKAGED ON TAPE & REEL

Positions: 04 thru 100

A = .050 [1.27] x No. of Positions per Row + .008 [0.20]

B = .050 [1.27] x No. of Spaces

C = .050 [1.27] x No. of (Spaces-1)

SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 1 Amp

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS DRAWN HR CHECKED AC APPROVED			DATE 11/26/18 11/26/18		TITLE .050" x .100" DUAL ROW RECEPTACLE STRIP .224 [5.70] HEIGHT, SURFACE MOUNT	
SIZE X			PART NO. HRS-2FY-XX-SG-SMT		REV. -	
REF: S00111C			SCALE: NTS		SHEET 1 OF 1	

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[HRS-2FY-10-SG-SMT](#) [HRS-2FY-20-SG-SMT](#) [HRS-2FY-12-SG-SMT](#) [HRS-2FY-06-SG-SMT](#) [HRS-2FY-18-SG-SMT](#)
[HRS-2FY-16-SG-SMT](#) [HRS-2FY-08-SG-SMT](#) [HRS-2FY-04-SG-SMT](#) [HRS-2FY-14-SG-SMT](#)