


APPROVED: _____


DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/22/22	
A		UPDATE TITLE	7/18/22	JJ/RC
B		ADDED COLOR	8/4/22	LH/RC
C		ADDED PAGE2	9/26/22	WX/LL1
D		ADDED SPEC.	8/23/23	LH/NL
E		ADDED SPEC.	4/1/24	JJ/NL



Product Dimensions

Part Number	Size		As supplied (mm)		After recovered (mm)			Standard Length (Meter)
	mm	Inch	I.D.(min) (D)	W.T. (Nominal Size) (W)	I.D.(max) (d)	W.T. (w)	Adhesive thickness	
Shrink ratio 3:1								
HST-A-032-XX-X-SR31	3.2	1/8	3.2	0.45	1.0	1.00±0.28	0.45±0.10	200
HST-A-048-XX-X-SR31	4.8	3/16	4.8	0.45	1.6	1.00±0.28	0.50±0.15	100
HST-A-064-XX-X-SR31	6.4	1/4	6.4	0.50	2.0	1.00±0.28	0.50±0.15	100
HST-A-095-XX-X-SR31	9.5	3/8	9.5	0.50	3.0	1.40±0.28	0.60±0.15	50
HST-A-127-XX-X-SR31	12.7	1/2	12.7	0.65	4.0	1.78±0.38	0.76±0.20	1.22
HST-A-150-XX-X-SR31	15.0	5/8	15.0	0.60	5.0	1.90±0.38	0.76±0.20	1.22
HST-A-191-XX-X-SR31	19.1	3/4	19.1	0.70	6.0	2.25±0.55	0.76±0.20	1.22
HST-A-254-XX-X-SR31	25.4	1	25.0	0.80	8.0	2.54±0.55	1.00±0.25	1.22
HST-A-381-XX-X-SR31	38.1	1 1/2	38.1	0.80	13.0	2.54±0.55	1.00±0.25	1.22



BEFORE SHRINKING

AFTER SHRINKING

HST-A-XXX-XX-X-SR31

TYPE SEE CHART

Color
BK=Black (Stocked)
WT=White (Special Order)
RD=Red (Special Order)
BU=Blue (Special Order)
YW=Yellow (Special Order)
GN=Green (Special Order)
BN=Brown (Special Order)
OR=Orange (Special Order)
VT=Violet (Special Order)
GY=Gray (Special Order)
CL=Clear (Special Order)

Length
4= 4FT(48"inch)
100= 100FT(1200"inch)
A= 50.8mm
B= 12.7mm

SPECIFICATIONS:
Material: Polyolefin, rated UL 94V-1
Electrical:
Shrinkage: 3:1
UL Style: UL224, 125°C VW-1 600V
Temperature Rating:
Operating temperature: -45°C to +110°C
Environmental:
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

DRAWN	LH	6/22/22
CHECKED	RC	6/22/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		
DUAL WALL ADHESIVE LINED HEAT SHRINK TUBING, FLAME RETARDANT POLYOLEFIN		
SIZE	PART NO.	REV.
X	HST-A-XXX-XX-X-SR31	E
REF:	-	SCALE: NTS
SHEET 1 OF 2		

6

5

4

3

2

1

Rev

AWO #

Description

Date



Appr

APPROVED: _____

DATE: _____ TITLE: _____

SEE SHT 1 OF 2 FOR REVISION

CARTON



PO:XXXXXXXX (SOXXXXXXXX)		ADAM TECH
ADAM TECH P/N: HST-A-XXX-XX-X-SR31		
Q TY: XXXX PCS		
LOT DTAE: XXXX		
		RoHS
POLYOLEFIN HEAT SHRINK TUBING		

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

DRAWN

LH

6/22/22

CHECKED

RC

6/22/22

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH**ADAM**
TECH909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

DUAL WALL ADHESIVE LINED HEAT SHRINK TUBING,
FLAME RETARDANT POLYOLEFINSIZE
X

PART NO.

HST-A-XXX-XX-X-SR31

REV.
E

REF:

-

SCALE: NTS

SHEET 2 OF 2

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[HST-A-191-BK-4-SR31](#) [HST-A-064-BK-4-SR31](#) [HST-A-095-BK-4-SR31](#) [HST-A-381-BK-4-SR31](#) [HST-A-150-BK-4-SR31](#) [HST-A-150-BH-4-SR31](#) [HST-A-254-BK-4-SR31](#) [HST-A-032-BK-4-SR31](#) [HST-A-127-BK-4-SR31](#) [HST-A-048-BK-4-SR31](#)