


APPROVED: _____


DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/22/22	
A		UPDATE TITLE	7/18/22	JJ/RC
B		ADDED COLOR	8/4/22	LH/RC
C		ADDED PAGE2	9/26/22	WX/RC



Product Dimensions

Part Number	Size		As supplied (mm)		After recovered (mm)			Standard Length (Meter)
	mm	Inch	I.D.(min) (D)	W.T. (Nominal Size) (W)	I.D.(max) (d)	W.T. (w)	Adhesive thickness	
Shrink ratio 4:1								
HST-A-040-XX-X-SR41	4	3/16	4.0	0.40	1.0	1.00±0.28	0.45±0.10	1.22
HST-A-080-XX-X-SR41	8	5/16	8.0	0.45	2.0	1.00±0.28	0.50±0.10	1.22
HST-A-120-XX-X-SR41	12	1/2	12.0	0.45	3.0	1.40±0.28	0.60±0.10	1.22
HST-A-160-XX-X-SR41	16	5/8	16.0	0.55	4.0	1.78±0.38	0.76±0.15	1.22
HST-A-240-XX-X-SR41	24	1	24.0	0.65	6.0	2.25±0.55	0.76±0.15	1.22
HST-A-320-XX-X-SR41	32	1 1/4	32.0	0.70	8.0	2.54±0.55	1.00±0.20	1.22
HST-A-500-XX-X-SR41	50	2	50.0	0.70	13.0	2.54±0.55	1.00±0.20	1.22



HST-A-XXX-XX-X-SR41

TYPE SEE CHART

Length

4= 4FT(48"inch)



Color
BK=Black (Stocked)
WT=White (Special Order)
RD=Red (Special Order)
BU=Blue (Special Order)
YW=Yellow (Special Order)
GN=Green (Special Order)

SPECIFICATIONS:

Material: Polyolefin

Electrical:

Shrinkage: 4:1

UL Style: UL224, 125°C VW-1 600V

Temperature Rating:

Operating temperature: -45°C to +110°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

DRAWN	LH	6/22/22
CHECKED	RC	6/22/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
DUAL WALL ADHESIVE LINED HEAT SHRINK TUBING,
FLAME RETARDANT POLYOLEFIN

SIZE	PART NO.	REV.
X	HST-A-XXX-XX-X-SR41	C
REF:	-	SCALE: NTS SHEET 1 OF 2

6

5

4

3

2

1

Rev

AWO #

Description

Date

Appr

APPROVED: _____

DATE: _____ TITLE: _____

SEE SHT 1 OF 2 FOR REVISION

D

D

C

C


B

B

A

A

CARTON



PO:XXXXXXXX (SOXXXXXXXX)	ADAM TECH
ADAM TECH P/N: HST-A-XXX-XX-X-SR41	
Q TY: XXXX PCS	
LOT DTAE: XXXX	
POLYOLEFIN HEAT SHRINK TUBING	RoHS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

DRAWN

LH

6/22/22

CHECKED

RC

6/22/22

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH**ADAM**
TECH909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

DUAL WALL ADHESIVE LINED HEAT SHRINK TUBING,
FLAME RETARDANT POLYOLEFINSIZE
X

PART NO.

HST-A-XXX-XX-X-SR41

REV.
C

REF: -

SCALE: NTS

SHEET 2 OF 2

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[HST-A-240-BK-4-SR31](#) [HST-A-080-BK-4-SR31](#) [HST-A-120-BK-4-SR41](#) [HST-A-500-BK-4-SR41](#) [HST-A-080-BK-4-SR41](#) [HST-A-320-BK-4-SR41](#) [HST-A-040-BK-4-SR41](#) [HST-A-160-BK-4-SR31](#) [HST-A-500-BK-4-SR31](#) [HST-A-240-BK-4-SR41](#) [HST-A-160-BK-4-SR41](#) [HST-A-320-BK-4-SR31](#) [HST-A-120-BK-4-SR31](#)