




APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/16/05	
A		REDRAWN	12/13/13	AY/GC
B		REVISED TERMINAL OPTIONS P/N	7/17/14	AY
C		UPDATE PANEL CUT-OUT DIM.	11/4/15	AY/MW
D		UPDATE PANEL TERMINAL OPTIONS	7/7/20	AY/RC



1.063 [27.00] Front Mounting  
1.213 [30.80] Rear Mounting



FOR REAR MOUNTING USE  
PANEL CUT-OUT

TERMINAL OPTIONS		
IEC-A-1	IEC-A-2	IEC-A-3
.187 Q.C.	.250 Q.C.	.157 Solder

#### SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Contact: Copper Alloy, Tin Plated

Electrical:

Rating: 15A @ 250V C-ULus

10A @ 250V ENEC & CCC

Insulation resistance: 100 Mohms min @ 500 VDC

Dielectric withstanding voltage: 3000 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE MM [INCHES]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES  
.X  $\pm .10$   $\phi .X$   $\pm .10$   
.XX  $\pm .020$   $\phi .XX$   $\pm .015$   
.XXX  $\pm .015$   $\phi .XXX$   $\pm .010$

APPROVALS		DATE
DRAWN	SS	6/16/05
CHECKED		
APPROVED		

**ADAM  
TECH  
INTERCONNECTS**

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE		
IEC, C14 MALE, PANEL MOUNT, FLANGED		
SIZE X	PART NO. IEC-A-X	REV. D
REF: S00087C	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[IEC-A-2](#)