





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/05	



SPECIFICATIONS:

Material:
 Insulator: Nylon 66, rated UL 94V-2
 Insulator color: White
 Contacts: Brass

Plating:
 Tin over Copper underplate overall

Electrical:
 Operating voltage: 250 VAC max
 Current rating: 3 Amps max
 Dielectric withstanding voltage: 1,500 VAC for 1 minute
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant



Positions: 2 thru 20

A = .100 [2.54] x No. of Positions

B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	4/8/05
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE
 .100 [2.54] LOCKING HEADER
 RIGHT ANGLE, PCB

SIZE	PART NO.	REV.
X	LHA-XX-TRA	-
REF:	S00123T	SCALE: NTS
		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[LHA-02-TRA](#) [LHA-03-TRA](#) [LHA-04-TRA](#) [LHA-05-TRA](#) [LHA-06-TRA](#) [LHA-08-TRA](#) [LHA-09-TRA](#) [LHA-10-TRA](#)
[LHA-13-TRA](#) [LHA-14-TRA](#) [LHA-11-TRA](#) [LHA-15-TRA](#) [LHA-07-TRA](#) [LHA-12-TRA](#)