





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/12/05	
A		REVISED DIM.	2/11/09	
B		UPDATE spec.	10/24/18	AY/TY



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 250V AC/DC

Current rating: 5 A AC/DC

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20

A = .156 [3.96] x No. of (Positions - 1)

B = .156 [3.96] x No. of positions

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	4/12/05
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.156 [3.96] POWER HEADER
RIGHT ANGLE, WITH LOCK POLARIZER

SIZE X	PART NO. LHB-XX-SB1	REV. B
REF: S00016T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[LHB-02-SB1](#) [LHB-03-SB1](#) [LHB-04-SB1](#) [LHB-05-SB1](#) [LHB-08-SB1](#) [LHB-10-SB1](#) [LHB-09-SB1](#) [LHB-07-SB1](#) [LHB-06-SB1](#)