





Rev	AWO #	Description	Date	Appr
-		RELEASED	6/18/10	
A		ECN	12/8/10	
B		REVISED DIM.	2/17/14	AY/MY

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



Positions: 2 thru 20

A = .156 [3.96] x No. of Positions

B = .156 [3.96] x No. of Spaces

SPECIFICATIONS:

Material:

Insulator: PA66, glass reinforced, rated UL 94V-2

Insulator color: White

contact: Brass, Tin or Ni plated

Electrical:

Current rating: 7 Amps max

Contact resistance: 20mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant



156 [3.96] HEADER, RIGHT ANGLE

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES				Holes			
.X	± .10	ØXX	± .10	.X	± .10	ØXX	± .10
.XX	± .020	ØXXX	± .015	.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXXX	± .010	.XXX	± .015	ØXXXX	± .010
APPROVALS				DATE			
DRAWN	DY		6/18/10				
CHECKED							
APPROVED							
				SIZE	PART NO.		REV.
				X	LHD-XX-TRA		B
				REF: S00019C	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[LHD-05-TRA](#) [LHD-06-TRA](#) [LHD-03-TRA](#) [LHD-08-TRA](#) [LHD-04-TRA](#) [LHD-10-TRA](#) [LHD-09-TRA](#) [LHD-02-TRA](#)
[LHD-07-TRA](#)