





APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



Rev	AWO #	Description	Date	Appr
-		RELEASED	6/17/11	
A		REVISED SHAPE	7/24/13	
B		REVISED DIM.	2/17/14	AY/MY

SPECIFICATIONS:
Material: PA66, glass reinforced, rated UL 94V-2
Insulator color: White
Insulator contact: Brass, Tin plated
Electrical:
Current rating: 7 Amps max
Contact resistance: 20mohms max
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating: Operating temperature: -40°C to +85°C
Environmental: Lead free, RoHS compliant



Positions: 2 thru 20
A = .156 [3.96] x No. of Positions
B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
.X	± .10	ØXX	± .10
.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXXX	± .010
APPROVALS		DATE	
DRAWN		DY	
CHECKED		6/17/11	
APPROVED			

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .156 [3.96] HEADER, REVERSE RIGHT ANGLE

SIZE	PART NO.	REV.
X	LHD-XX-TRB	B
REF: S00019C		SCALE: NTS
SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[LHD-10-TRB](#) [LHD-02-TRB](#) [LHD-04-TRB](#) [LHD-05-TRB](#) [LHD-09-TRB](#) [LHD-07-TRB](#) [LHD-08-TRB](#) [LHD-03-TRB](#)
[LHD-06-TRB](#)