





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/4/09	
A		REDRAWN	10/7/10	
B		UPDATE DIM.	8/31/20	LH/EY



SPECIFICATIONS:

Material:

Insulator: Nylon PA66, rated UL 94V-2

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Current rating: 7 Amps max

Contact Resistance: 20 mohms max.

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20

A = .156 [3.96] x No. of Positions

B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	1/4/09
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
.156 [3.96] HEADER, STRAIGHT			
SIZE	PART NO.	REV.	
X	LHD-XX-TS	B	
REF:	S00019C	SCALE:	NTS
SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[LHD-08-TS](#) [LHD-04-TS](#) [LHD-02-TS](#) [LHD-09-TS](#) [LHD-03-TS](#) [LHD-06-TS](#) [LHD-07-TS](#) [LHD-10-TS](#) [LHD-05-TS](#)