





Rev	AWO #	Description	Date	Appr
-		RELEASED	12/08/10	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250V AC,DC

Current rating: 7A AC,DC

Contact resistance: 10 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 10
A = .200 [5.08] x No. of Positions
B = .200 [5.08] x No. of Spaces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

.200 [5.08] POWER HEADER, STRAIGHT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				TITLE			
.X	± .10	ØXX	± .10	909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
.XX	± .020	ØXXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS		DATE		.200 [5.08] POWER HEADER, STRAIGHT			
DRAWN	DY	12/08/10					
CHECKED							
APPROVED							
SIZE		PART NO.		LHF-XX-SA2			
X							
REF: S00099T							
SCALE: NTS		SHEET 1 OF 1		REV: -			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[LHF-04-SA2](#) [LHF-05-SA2](#) [LHF-03-SA2](#) [LHF-06-SA2](#)