







APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/20/18	



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:  
Insulator: Hi-temp thermoplastic, rated UL 94V-0  
Insulator color: Black  
Contacts: Copper Alloy  
Shell: Stainless Steel, Nickel plated,  
Gold over Nickel underplate on solder tails  
Plating:  
Gold flash over Nickel underplate overall  
Electrical:  
Contact resistance: 30 milliohms max.  
Insulation resistance: 1,000 Megohms min.  
Dielectric withstand voltage: 100 VAC for 1 minute  
Environmental:  
Ingress protection rating: IPX5  
Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES                      HOLES .X           ± .10                      Ø.X           ±.10 .XX          ± .020                    Ø.XX          ± .015 .XXX       ± .015                    Ø.XXX       ±.010				<div>ADAM TECH</div> INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		TITLE					
DRAWN		HR		DATE		9/20/18	
CHECKED		LW		DATE		9/20/18	
APPROVED							
SIZE		PART NO.		REV.			
X		MCR-B-S-RA-TSMT-CS1-WP-T/R		-			
REF:		S00005C		SCALE: NTS		SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MCR-B-S-RA-TSMT-CS1-WP-T/R](#)