





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/9/10	
A		ADDED TOLERANCE (ED-20140311-ECN-01)	3/11/14	HR/CH
B		UPDATE DRAWING	9/18/20	AY/RC



RECOMMENDED TOLERANCE: ± 0.001 [0.03]



SPECIFICATIONS:

Material:

Insulator: PBT, glass filled, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shield: Brass, Tin plated

Plating:

Gold flash over Nickel underplate on contact area,

Tin over Nickel underplate on tails

Electrical:

Rated Voltage And Current: DC12V/2A Max., AC100V/1A Max.

Contact resistance: 30 mohms max.

Insulation resistance: 100 Mohms min @ 500 VDC

Dielectric withstanding voltage: 250 VAC for 1 minute

Environmental:

Lead free, RoHS Compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X $\pm .10$ \varnothing .X $\pm .10$
.XX $\pm .020$ \varnothing .XX $\pm .015$
.XXX $\pm .015$ \varnothing .XXX $\pm .010$

APPROVALS		DATE
DRAWN	AY	12/9/10
CHECKED	SC	12/9/10
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
MINI DIN JACK, RIGHT ANGLE, FULL SHIELD			
SIZE X	PART NO. MDJ-009-FS	REV. B	
REF: S00095T	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MDJ-009-FS](#)