


APPROVED: _____


DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/25/10	
A		ADDED DRAWING	12/25/18	AY/RC1
B		ADDED DRAWING	12/23/21	JJ/JL1




60, 64 PIN



20, 24, 26, 30, 34, 40, 50 PIN



10, 14, 16 PIN



Positions: 10, 14, 16, 20, 24, 26, 30, 34, 40, 50, 60, 64

A = .100 [2.54] x No. of Spaces + .855 [21.71]

B = .100 [2.54] x No. of Spaces + .454 [11.54]

C = .100 [2.54] x No. of Spaces

D = .100 [2.54] x No. of Spaces + .305 [7.74]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	Holes
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

DRAWN	DY	3/25/10
CHECKED		
APPROVED		

TITLE	LATCH BOX HEADER, VERTICAL TYPE LONG EJECTOR LATCHES		
SIZE	PART NO.	MHR-XX-VUAL	
REF:	S00059T	SCALE: NTS	SHEET 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

REV.	B
------	---

SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0, Color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 1 Amp

Contact Resistance: 10 mohm max

Insulation resistance: 1000 Mohm min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MHR-34-VUAL](#) [MHR-26-VUAL](#) [MHR-40-VUAL](#) [MHR-50-VUAL](#) [MHR-10-VUAL](#) [MHR-30-VUAL](#) [MHR-24-VUAL](#)
[MHR-20-VUAL](#) [MHR-60-VUAL](#) [MHR-14-VUAL](#)