


APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/16/21	



NOTE; BEND RELIEF
MUST BE ORDERED
SEPARATELY




ALIGNMENT KEY
G = 0

MMI-P1FGXXSXXXB

BODY COLOR
B = BLACK
G = GRAY

CABLE COLLET SIZE
39 = 2.7mm ~ 3.9mm ID
52 = 4.0mm ~ 5.2mm ID
65 = 5.3mm ~ 6.5mm ID

OF POSITIONS
02,. 03, 04, 05, 06, 07, 08, 09, 10 & 14



	2 Pin	3 Pin	4 Pin	5 Pin	6 Pin	7 Pin	8 Pin	9 Pin	10 Pin	14 Pin
Configuration										
Diameter of Pin	1.3	1.3	0.9	0.9	0.7	0.7	0.7	0.5	0.5	0.5
Testing Voltage	1200V	1200V	1200V	1200V	1000V	1000V	1000V	800V	800V	800V
Working Voltage	300V	300V	250V	250V	200V	200V	200V	200V	200V	200V
Rated Current / Pin	20A	12A	10A	9A	8A	7A	6A	4A	4A	4A

SPECIFICATIONS:

Material:

Housing (Body): PC

Insulator: PPS

Terminal: Brass, Gold Plated

Electrical:

Voltage Rating: See chart

Current Rating: See chart

Dielectric withstanding voltage: See chart

Electrical Life: 1,000 Cycles min.

Temperature Rating:

Operating temperature: -55°C to +118°C

Environmental:

IP50 Protection (Mated Condition)

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	8/16/21
CHECKED	SS	8/16/21
APPROVED		

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
PUSH-PULL CONNECTOR FEMALE PLUG, PLASTIC,
SIZE 1, SOLDER TERMINAL, BEND RELIEF TYPE, IP50

SIZE	PART NO.	REV.
X	MMI-P1FGXXSXXXB	-
REF:	SXXXXX	SCALE: NTS
SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MMI-P1FG06SG52B](#) [MMI-P1FG07SG52B](#) [MMI-P1FG02SG52B](#) [MMI-P1FG08SG52B](#) [MMI-P1FG10SG52B](#) [MMI-P1FG03SG52B](#) [MMI-P1FG05SG52B](#) [MMI-P1FG04SG52B](#)