

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description

Date

Appr

-

RELEASED

8/16/21

D

D

C



C

B

B

A

A

REF.
.157 [4.0]REF
Ø.716
[Ø18.2]

M14X1.0

MMI-P1S-FN-X

BACK NUT COLOR
B = BLACK
G = GRAY
GR = GREEN
Y = YELLOW
R = RED
BU = BLUE

SPECIFICATIONS:

Material:

Back Nut: PC

Temperature Rating:

Operating temperature: -55°C to +118°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	8/16/21
CHECKED	SS	8/16/21
APPROVED		

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
PUSH-PULL SOCKET, FRONT NUT PLASTIC, SIZE 1			
SIZE X	PART NO. MMI-P1S-FN-X	REV. -	
REF: SXXXXXX	SCALE: NTS	SHEET 1 OF 1	

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MMI-P1RSG03SGG](#) [MMI-P1RSG06SGG](#) [MMI-P1RSG04SGG](#) [MMI-P1RSG07SGG](#) [MMI-P1RSG05SGG](#) [MMI-P1RSG02SGG](#)