




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/1/05	
A		REVISED SHAPE	12/18/12	



SPECIFICATIONS:

Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating:
G = Gold flash over Nickel underplate overall
T = Tin over Copper underplate overall
Electrical:
Operating voltage: 250 VAC max
Current rating: 1 Amp max
Contact resistance: 20 mohms max
Insulation resistance: 5,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -55°C to +105°C
Environmental:
Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.079 [2.00] MINI SHUNT, OPEN TOP
.138 [3.50] HEIGHT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED							
INCHES				HOLES			
.X ± .10				ØX ± .10			
.XX ± .020				ØXXX ± .015			
.XXX ± .015				ØXXX ± .010			
APPROVALS				DATE			
DRAWN				SS			
				4/1/05			
CHECKED							
APPROVED							
SIZE		PART NO.		SCALE		SHEET 1 OF 1	
X		MS2B-X		NTS		A	
REF:							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MS2B-G](#) [MS2B-T](#)